ON Semiconductor

Is Now

onsemi™

To learn more about onsemi™, please visit our website at
www.onsemi.com

74VCX16373

Low-Voltage 1.8/2.5/3.3V 16-Bit Transparent Latch

With 3.6 V−Tolerant Inputs and Outputs (3−State, Non−Inverting)

The 74VCX16373 is an advanced performance, non−inverting 16−bit transparent latch. It is designed for very high−speed, very low−power operation in 1.8 V, 2.5 V or 3.3 V systems. The VCX16373 is byte controlled, with each byte functioning identically, but independently. Each byte has separate Output Enable and Latch Enable inputs. These control pins can be tied together for full 16−bit operation.

When operating at 2.5 V (or 1.8 V) the part is designed to tolerate voltages it may encounter on either inputs or outputs when interfacing to 3.3 V busses. It is guaranteed to be overvoltage tolerant to 3.6 V.

The 74VCX16373 contains 16 D−type latches with 3−state 3.6 V−tolerant outputs. When the Latch Enable (LEn) inputs are HIGH, data on the Dn inputs enters the latches. In this condition, the latches are transparent, (a latch output will change state each time its D input changes). When LE is LOW, the latch stores the information that was present on the D inputs a setup time preceding the HIGH−to−LOW transition of LE. The 3−state outputs are controlled by the Output Enable ($\overline{\text{OEn}}$) inputs. When $\overline{\text{OE}}$ is LOW, the outputs are enabled. When $\overline{\text{OE}}$ is HIGH, the standard outputs are in the high impedance state, but this does not interfere with new data entering into the latches.

Features

- Designed for Low Voltage Operation: V_{CC} = 1.65 V − 3.6 V
- 3.6 V Tolerant Inputs and Outputs
- High Speed Operation: 3.0 ns max for 3.0 V to 3.6 V
  3.9 ns max for 2.3 V to 2.7 V
  6.8 ns max for 1.65 V to 1.95 V
- Static Drive: ±24 mA Drive at 3.0 V
  ±18 mA Drive at 2.3 V
  ±6 mA Drive at 1.65 V
- Supports Live Insertion and Withdrawal
- I_{OFF} Specification Guarantees High Impedance When V_{CC} = 0 V
- Near Zero Static Supply Current in All Three Logic States (20 µA) Substantially Reduces System Power Requirements
- Latchup Performance Exceeds ±250 mA @ 125°C
- ESD Performance: Human Body Model >2000 V;
  Machine Model >200 V
- All Devices in Package TSSOP are Inherently Pb−Free*

*For additional information on our Pb−Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor®

http://onsemi.com

MARKING DIAGRAM

48

TSSOP−48
DT SUFFIX
CASE 1201

```
VCX16373
AWLYYWW
```

A   = Assembly Location
WL = Wafer Lot
YY = Year
WW = Work Week

PIN NAMES

Pins	Function
$\overline{\text{OEn}}$	Output Enable Inputs
LEn	Latch Enable Inputs
D0–D15	Inputs
O0–O15	Outputs

ORDERING INFORMATION

Device	Package	Shipping[†]
74VCX16373DT	TSSOP (Pb−Free)	39 / Rail
74VCX16373DTR	TSSOP (Pb−Free)	2500 / Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

74VCX16373

Figure 1. 48−Lead Pinout
(Top View)

Figure 2. Logic Diagram

Figure 3. IEC Logic Diagram

74VCX16373

TRUTH TABLE

Inputs			Outputs	Inputs			Outputs
LE1	OE1	D0:7	O0:7	LE2	OE2	D8:15	O8:15
X	H	X	Z	X	H	X	Z
H	L	L	L	H	L	L	L
H	L	H	H	H	L	H	H
L.	L	X	O0	L	L	X	O0

H = High Voltage Level
L = Low Voltage Level
Z = High Impedance State
X = High or Low Voltage Level and Transitions Are Acceptable, for I_{CC} reasons, DO NOT FLOAT Inputs
O0 = No Change

ABSOLUTE MAXIMUM RATINGS

| Symbol	Parameter	Value	Condition	Unit
V_{CC}	DC Supply Voltage	−0.5 to +4.6		V
V_I	DC Input Voltage	$-0.5 \leq V_I \leq +4.6$		V
V_O	DC Output Voltage	$-0.5 \leq V_O \leq +4.6$	Output in 3−State	V
		$-0.5 \leq V_O \leq V_{CC} + 0.5$	Note 1; Outputs Active	
I_{IK}	DC Input Diode Current	−50	V_I < GND	mA
I_{OK}	DC Output Diode Current	−50	V_O < GND	mA
		+50	V_O > V_{CC}	
I_O	DC Output Source/Sink Current	±50		mA
I_{CC}	DC Supply Current Per Supply Pin	±100		mA
I_{GND}	DC Ground Current Per Ground Pin	±100		mA
T_{STG}	Storage Temperature Range	−65 to +150		°C

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.
1. I_O absolute maximum rating must be observed.

RECOMMENDED OPERATING CONDITIONS

Symbol	Parameter		Min	Typ	Max	Unit
V_{CC}	Supply Voltage	Operating	1.65	3.3	3.6	V
		Data Retention Only	1.2	3.3	3.6	
V_I	Input Voltage		−0.3		3.6	V
V_O	Output Voltage	(Active State)	0		V_{CC}	V
		(3−State)	0		3.6	
I_{OH}	HIGH Level Output Current, V_{CC} = 3.0 V – 3.6 V				−24	mA
I_{OL}	LOW Level Output Current, V_{CC} = 3.0 V – 3.6 V				24	mA
I_{OH}	HIGH Level Output Current, V_{CC} = 2.3 V – 2.7 V				−18	mA
I_{OL}	LOW Level Output Current, V_{CC} = 2.3 V – 2.7 V				18	mA
I_{OH}	HIGH Level Output Current, V_{CC} = 1.65 V – 1.95 V				−6	mA
I_{OL}	LOW Level Output Current, V_{CC} = 1.65 V – 1.95 V				6	mA
T_A	Operating Free−Air Temperature		−40		+85	°C
$\Delta t/\Delta V$	Input Transition Rise or Fall Rate, V_{IN} from 0.8 V to 2.0 V, V_{CC} = 3.0 V		0		10	ns/V

74VCX16373

DC ELECTRICAL CHARACTERISTICS

Symbol	Characteristic	Condition	T_A = −40°C to +85°C Min	T_A = −40°C to +85°C Max	Unit
V_{IH}	HIGH Level Input Voltage (Note 2)	1.65 V ≤ V_{CC} < 2.3 V	0.65 x V_{CC}		V
		2.3 V ≤ V_{CC} ≤ 2.7 V	1.6		
		2.7 V < V_{CC} ≤ 3.6 V	2.0		
V_{IL}	LOW Level Input Voltage (Note 2)	1.65 V ≤ V_{CC} < 2.3 V		0.35 x V_{CC}	V
		2.3 V ≤ V_{CC} ≤ 2.7 V		0.7	
		2.7 V < V_{CC} ≤ 3.6 V		0.8	
V_{OH}	HIGH Level Output Voltage	1.65 V ≤ V_{CC} ≤ 3.6 V; I_{OH} = −100 μA	V_{CC} − 0.2		V
		V_{CC} = 1.65 V; I_{OH} = −6 mA	1.25		
		V_{CC} = 2.3 V; I_{OH} = −6 mA	2.0		
		V_{CC} = 2.3 V; I_{OH} = −12 mA	1.8		
		V_{CC} = 2.3 V; I_{OH} = −18 mA	1.7		
		V_{CC} = 2.7 V; I_{OH} = −12 mA	2.2		
		V_{CC} = 3.0 V; I_{OH} = −18 mA	2.4		
		V_{CC} = 3.0 V; I_{OH} = −24 mA	2.2		
V_{OL}	LOW Level Output Voltage	1.65 V ≤ V_{CC} ≤ 3.6 V; I_{OL} = 100 μA		0.2	V
		V_{CC} = 1.65 V; I_{OL} = 6 mA		0.3	
		V_{CC} = 2.3 V; I_{OL} = 12 mA		0.4	
		V_{CC} = 2.3 V; I_{OL} = 18 mA		0.6	
		V_{CC} = 2.7 V; I_{OL} = 12 mA		0.4	
		V_{CC} = 3.0 V; I_{OL} = 18 mA		0.4	
		V_{CC} = 3.0 V; I_{OL} = 24 mA		0.55	
I_I	Input Leakage Current	1.65 V ≤ V_{CC} ≤ 3.6 V; 0 V ≤ V_I ≤ 3.6 V		±5.0	μA
I_{OZ}	3−State Output Current	1.65 V ≤ V_{CC} ≤ 3.6 V; 0 V ≤ V_O ≤ 3.6 V; V_I = V_{IH} or V_{IL}		±10	μA
I_{OFF}	Power−Off Leakage Current	V_{CC} = 0 V; V_I or V_O = 3.6 V		10	μA
I_{CC}	Quiescent Supply Current (Note 3)	1.65 V ≤ V_{CC} ≤ 3.6 V; V_I = GND or V_{CC}		20	μA
		1.65 V ≤ V_{CC} ≤ 3.6 V; 3.6 V ≤ V_I, V_O ≤ 3.6 V		±20	μA
ΔI_{CC}	Increase in I_{CC} per Input	2.7 V < V_{CC} ≤ 3.6 V; V_{IH} = V_{CC} − 0.6 V		750	μA

2. These values of V_I are used to test DC electrical characteristics only.
3. Outputs disabled or 3−state only.

74VCX16373

AC CHARACTERISTICS (Note 4; $t_R = t_F$ = 2.0 ns; C_L = 30 pF; R_L = 500 Ω)

Symbol	Parameter	Waveform	V_{CC} = 3.0 V to 3.6 V		V_{CC} = 2.3 V to 2.7 V		V_{CC} = 1.65 V to 1.95 V		Unit
			Min	Max	Min	Max	Min	Max	
t_{PLH} t_{PHL}	Propagation Delay Dn–to–On	1	0.8 0.8	3.0 3.0	1.0 1.0	3.4 3.4	1.5 1.5	6.8 6.8	ns
t_{PLH} t_{PHL}	Propagation Delay LE–to–On	1	0.8 0.8	3.0 3.0	1.0 1.0	3.9 3.9	1.5 1.5	7.8 7.8	ns
t_{PZH} t_{PZL}	Output Enable Time to High and Low Level	2	0.8 0.8	3.5 3.5	1.0 1.0	4.6 4.6	1.5 1.5	9.2 9.2	ns
t_{PHZ} t_{PLZ}	Output Disable Time From High and Low Level	2	0.8 0.8	3.5 3.5	1.0 1.0	3.8 3.8	1.5 1.5	6.8 6.8	ns
t_s	Setup Time, High or Low Dn–to–LE	3	1.5		1.5		2.5		ns
t_h	Hold Time, High or Low Dn–to–LE	3	1.0		1.0		1.0		ns
t_w	LE Pulse Width, High	3	1.5		1.5		4.0		ns
t_{OSHL} t_{OSLH}	Output–to–Output Skew (Note 5)			0.5 0.5		0.5 0.5		0.75 0.75	ns

4. For C_L = 50 pF, add approximately 300 ps to the AC maximum specification.
5. Skew is defined as the absolute value of the difference between the actual propagation delay for any two separate outputs of the same device. The specification applies to any outputs switching in the same direction, either HIGH–to–LOW (t_{OSHL}) or LOW–to–HIGH (t_{OSLH}); parameter guaranteed by design.

AC CHARACTERISTICS ($t_R = t_F$ = 2.0 ns; C_L = 50 pF; R_L = 500 Ω)

Symbol	Parameter	Waveform	V_{CC} = 3.0 V to 3.6 V		V_{CC} = 2.7 V		Unit
			Min	Max	Min	Max	
t_{PLH} t_{PHL}	Propagation Delay Dn–to–On	4	1.0 1.0	3.6 3.6		4.3 4.3	ns
t_{PLH} t_{PHL}	Propagation Delay LE–to–On	4	1.0 1.0	3.9 3.9		4.6 4.6	ns
t_{PZH} t_{PZL}	Output Enable Time to High and Low Level	5	1.0 1.0	4.7 4.7		5.7 5.7	ns
t_{PHZ} t_{PLZ}	Output Disable Time From High and Low Level	5	1.0 1.0	4.1 4.1		4.5 4.5	ns
t_{OSHL} t_{OSLH}	Output–to–Output Skew (Note 6)			0.5 0.5		0.5 0.5	ns

6. Skew is defined as the absolute value of the difference between the actual propagation delay for any two separate outputs of the same device. The specification applies to any outputs switching in the same direction, either HIGH–to–LOW (t_{OSHL}) or LOW–to–HIGH (t_{OSLH}); parameter guaranteed by design.

74VCX16373

DYNAMIC SWITCHING CHARACTERISTICS

Symbol	Characteristic	Condition	T_A = +25°C Typ	Unit
V_{OLP}	Dynamic LOW Peak Voltage (Note 7)	V_{CC} = 1.8 V, C_L = 30 pF, V_{IH} = V_{CC}, V_{IL} = 0 V	0.25	V
		V_{CC} = 2.5 V, C_L = 30 pF, V_{IH} = V_{CC}, V_{IL} = 0 V	0.6	
		V_{CC} = 3.3 V, C_L = 30 pF, V_{IH} = V_{CC}, V_{IL} = 0 V	0.8	
V_{OLV}	Dynamic LOW Valley Voltage (Note 7)	V_{CC} = 1.8 V, C_L = 30 pF, V_{IH} = V_{CC}, V_{IL} = 0 V	−0.25	V
		V_{CC} = 2.5 V, C_L = 30 pF, V_{IH} = V_{CC}, V_{IL} = 0 V	−0.6	
		V_{CC} = 3.3 V, C_L = 30 pF, V_{IH} = V_{CC}, V_{IL} = 0 V	−0.8	
V_{OHV}	Dynamic HIGH Valley Voltage (Note 8)	V_{CC} = 1.8 V, C_L = 30 pF, V_{IH} = V_{CC}, V_{IL} = 0 V	1.5	V
		V_{CC} = 2.5 V, C_L = 30 pF, V_{IH} = V_{CC}, V_{IL} = 0 V	1.9	
		V_{CC} = 3.3 V, C_L = 30 pF, V_{IH} = V_{CC}, V_{IL} = 0 V	2.2	

7. Number of outputs defined as "n". Measured with "n−1" outputs switching from HIGH–to–LOW or LOW–to–HIGH. The remaining output is measured in the LOW state.
8. Number of outputs defined as "n". Measured with "n−1" outputs switching from HIGH–to–LOW or LOW–to–HIGH. The remaining output is measured in the HIGH state.

CAPACITIVE CHARACTERISTICS

| Symbol	Parameter	Condition	Typical	Unit
C_{IN}	Input Capacitance	Note 9	6	pF
C_{OUT}	Output Capacitance	Note 9	7	pF
C_{PD}	Power Dissipation Capacitance	Note 9, 10 MHz	20	pF

9. V_{CC} = 1.8 V, 2.5 V or 3.3 V; V_I = 0 V or V_{CC}.

WAVEFORM 1 – PROPAGATION DELAYS
t_R = t_F = 2.0 ns, 10% to 90%; f = 1 MHz; t_W = 500 ns
**Figure 4. AC Waveforms**

WAVEFORM 2 – OUTPUT ENABLE AND DISABLE TIMES
$t_R = t_F$ = 2.0 ns, 10% to 90%; f = 1 MHz; t_W = 500 ns

WAVEFORM 3 – LE to On PROPAGATION DELAYS, LE MINIMUM
PULSE WIDTH, Dn to LE SETUP AND HOLD TIMES
$t_R = t_F$ = 2.0 ns, 10% to 90%; f = 1 MHz; t_W = 500 ns except when noted

Figure 5. AC Waveforms

Table 1. AC WAVEFORMS

Symbol	V_{CC}		
	3.3 V ± 0.3 V	2.5 V ± 0.2 V	1.8 V ± 0.15 V
V_{IH}	2.7 V	V_{CC}	V_{CC}
V_m	1.5 V	$V_{CC}/2$	$V_{CC}/2$
V_x	V_{OL} + 0.3 V	V_{OL} + 0.15 V	V_{OL} + 0.15 V
V_y	V_{OH} − 0.3 V	V_{OH} − 0.15 V	V_{OH} − 0.15 V

Figure 6. Test Circuit

Table 2. TEST CIRCUIT

TEST	SWITCH
t_{PLH}, t_{PHL}	Open
t_{PZL}, t_{PLZ}	6 V at V_{CC} = 3.3 ± 0.3 V; V_{CC} × 2 at V_{CC} = 2.5 ± 0.2 V; 1.8 ± 0.15 V
t_{PZH}, t_{PHZ}	GND

C_L = 30 pF or equivalent (Includes jig and probe capacitance)
R_L = 500 Ω or equivalent
R_T = Z_{OUT} of pulse generator (typically 50 Ω)

74VCX16373

WAVEFORM 4 – PROPAGATION DELAYS
$t_R = t_F = 2.0$ ns, 10% to 90%; $f = 1$ MHz; $t_W = 500$ n**s**

Figure 7. AC Waveforms

WAVEFORM 5 – OUTPUT ENABLE AND DISABLE TIMES
$t_R = t_F = 2.0$ ns, 10% to 90%; $f = 1$ MHz; $t_W = 500$ ns

WAVEFORM 6 – LE to On PROPAGATION DELAYS, LE MINIMUM
PULSE WIDTH, Dn to LE SETUP AND HOLD TIMES
$t_R = t_F = 2.0$n s, 10% to 90%; $f = 1$ MHz; $t_W = 500$ ns
except when noted

Figure 8. AC Waveforms

Table 3. AC WAVEFORMS

Symbol	V_{CC}	
	3.3 V $\pm$ 0.3 V	**2.7 V**
V_{IH}	2.7 V	2.7 V
V_m	1.5 V	1.5 V
V_x	$V_{OL} + 0.3$ V	$V_{OL} + 0.3$ V
V_y	$V_{OH} - 0.3$ V	$V_{OH} - 0.3$ V

Figure 9. Test Circuit

Table 4. TEST CIRCUIT

TEST	SWITCH
t_{PLH}, t_{PHL}	Open
t_{PZL}, t_{PLZ}	6 V at $V_{CC} = 3.3 \pm 0.3$ V; $V_{CC} \times 2$ at $V_{CC} = 2.5 \pm 0.2$ V; 1.8 ± 0.15 V
t_{PZH}, t_{PHZ}	GND

C_L = 50 pF or equivalent (Includes jig and probe capacitance)
R_L = 500 Ω or equivalent
R_T = Z_{OUT} of pulse generator (typically 50Ω)

74VCX16373

PACKAGE DIMENSIONS

TSSOP
DT SUFFIX
CASE 1201–01
ISSUE A

NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETER.
3. DIMENSIONS A AND B DO NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS. MOLD FLASH OR GATE BURRS SHALL NOT EXCEED 0.15 (0.006) PER SIDE.
4. DIMENSION K DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE 0.08 (0.003) TOTAL IN EXCESS OF THE K DIMENSION AT MAXIMUM MATERIAL CONDITION.
5. TERMINAL NUMBERS ARE SHOWN FOR REFERENCE ONLY.
6. DIMENSIONS A AND B ARE TO BE DETERMINED AT DATUM PLANE –W–.

DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	12.40	12.60	0.488	0.496
B	6.00	6.20	0.236	0.244
C	---	1.10	---	0.043
D	0.05	0.15	0.002	0.006
F	0.50	0.75	0.020	0.030
G	0.50 BSC		0.0197 BSC	
H	0.37	---	0.015	---
J	0.09	0.20	0.004	0.008
J1	0.09	0.16	0.004	0.006
K	0.17	0.27	0.007	0.011
K1	0.17	0.23	0.007	0.009
L	7.95	8.25	0.313	0.325
M	0 °	8 °	0 °	8 °

PUBLICATION ORDERING INFORMATION

74VCX16373/D