onsemi

<u>Silicon Carbide (SiC)</u> <u>MOSFET</u> – EliteSiC, 80 mohm, 1200 V, M1, D2PAK-7L

NTBG080N120SC1

Features

- Typ. $R_{DS(on)} = 80 \text{ m}\Omega$
- Ultra Low Gate Charge (Typ. $Q_{G(tot)} = 56 \text{ nC}$)
- Low Effective Output Capacitance (Typ. Coss = 79 pF)
- 100% Avalanche Tested
- $T_J = 175^{\circ}C$
- This Device is Halide Free and RoHS Compliant with exemption 7a, Pb–Free 2LI (on second level interconnection)

Typical Applications

- UPS
- DC-DC Converter
- Boost Inverter

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Parameter			Symbol	Value	Unit
Drain-to-Source Voltage			V _{DSS}	1200	V
Gate-to-Source Voltag	ge		V _{GS}	-15/+25	V
Recommended Operation T _C < 175 Values of Gate–Source Voltage		T _C < 175°C	V _{GSop}	-5/+20	V
Continuous Drain Current (Note 1)	Steady State	Steady T _C = 25°C State		30	A
Power Dissipation (Note 1)			P _D	179	W
Continuous Drain Current (Note 1)	Steady T _C = 100°C State		۱ _D	21	A
Power Dissipation (Note 1)			P _D	89	W
Pulsed Drain Current (Note 2) $T_C = 25^{\circ}C$		I _{DM}	110	А	
Operating Junction and Storage Temperature Range			T _J , T _{stg}	–55 to +175	°C
Source Current (Body Diode)			۱ _S	18	А
Single Pulse Drain-to-Source Avalanche Energy (I _L = 18.5 A _{pk} , L = 1 mH) (Note 3)			E _{AS}	171	mJ
Maximum Lead Temperature for Soldering, 1/8" from Case for 10 Seconds			ΤL	300	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

 The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
Propertitive rating limited by max junction tomperature.

Repetitive rating, limited by max junction temperature.
E_{AS} of 171 mJ is based on starting T_J = 25°C; L = 1 mH, I_{AS} = 18.5 A, V_{AS} = 120 V V_{AS} = 18 V

V_{DD} = 120 V, V_{GS} = 18 V.

V _{(BR)DSS}	R _{DS(ON)} MAX	I _D MAX
1200 V	110 m Ω @ 20 V	30 A



N-CHANNEL MOSFET



D2PAK-7L CASE 418BJ

MARKING DIAGRAM

AYWWZZ NTBG 080120SC1

A = Assembly Location

- Y = Year
- WW = Work Week
- ZZ = Lot Traceability

NTBG080120SC1 = Specific Device Code

ORDERING INFORMATION

Device	Package	Shipping [†]
NTBG080N120SC1	D2PAK-7L	800 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, <u>BRD8011/D</u>.

Table 1. THERMAL CHARACTERISTICS

Parameter	Symbol	Мах	Unit
Thermal Resistance Junction-to-Case (Note 1)	$R_{ extsf{ heta}JC}$	0.84	°C/W
Thermal Resistance Junction-to-Ambient (Note 1)	$R_{ hetaJA}$	40	°C/W

Table 2. ELECTRICAL CHARACTERISTICS (T₁ = 25°C unless otherwise stated)

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
OFF CHARACTERISTICS	•		•		•	
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	$V_{GS} = 0 V, I_{D} = 1 mA$	1200			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} /T _J	I _D = 1 mA, refer to 25°C		0.5		V/°C
Zero Gate Voltage Drain Current	I _{DSS}	$V_{GS} = 0 V, T_J = 25^{\circ}C$			100	μΑ
		$I_{\rm J} = 175^{\circ}{\rm C}$			1	mA
	IGSS	V _{GS} = +25/-15 V, V _{DS} = 0 V			±1	μA
ON CHARACTERISTICS (Note 2)	1			T	r –	
Gate Threshold Voltage	V _{GS(TH)}	$V_{GS} = V_{DS}, I_D = 5 \text{ mA}$	1.8	3	4.3	V
Recommended Gate Voltage	V _{GOP}		-5		+20	V
Drain-to-Source On Resistance	R _{DS(on)}	V_{GS} = 20 V, I _D = 20 A, T _J = 25°C		80	110	mΩ
		V_{GS} = 20 V, I_D = 20 A, T_J = 150°C		121		mΩ
Forward Transconductance	9FS	$V_{DS} = 20 \text{ V}, \text{ I}_{D} = 20 \text{ A}$		11		S
CHARGES, CAPACITANCES & GATE RES	ISTANCE					
Input Capacitance	C _{ISS}	$V_{GS} = 0 V, f = 1 MHz,$		1154		pF
Output Capacitance	C _{OSS}	V _{DS} = 800 V		79		
Reverse Transfer Capacitance	C _{RSS}			7.9		
Total Gate Charge	Q _{G(TOT)}	$V_{GS} = -5/20 \text{ V}, V_{DS} = 600 \text{ V},$		56		nC
Threshold Gate Charge	Q _{G(TH)}	I _D = 20 A		10		
Gate-to-Source Charge	Q _{GS}			18		
Gate-to-Drain Charge	Q _{GD}			11		
Gate-Resistance	R _G	f = 1 MHz		1.2		Ω
SWITCHING CHARACTERISTICS						
Turn-On Delay Time	t _{d(ON)}	$V_{GS} = -5/20$ V, $V_{DS} = 800$ V,		12	22	ns
Rise Time	t _r	· I _D = 20 A, R _G = 4.7 Ω, Inductive Load		12	22	
Turn-Off Delay Time	t _{d(OFF)}			21	34	
Fall Time	t _f			9	18	
Turn-On Switching Loss	E _{ON}			135		μJ
Turn–Off Switching Loss	E _{OFF}			46		
Total Switching Loss	E _{TOT}			181		
DRAIN-SOURCE DIODE CHARACTERIST	ics		•		•	
Continuous Drain-Source Diode Forward Current	I _{SD}	V_{GS} = -5 V, T _J = 25°C			18	А
Pulsed Drain-Source Diode Forward Current (Note 2)	I _{SDM}	V_{GS} = -5 V, T _J = 25°C			110	А
Forward Diode Voltage	V _{SD}	$V_{GS} = -5 \text{ V}, \text{ I}_{SD} = 10 \text{ A}, \text{ T}_{\text{J}} = 25^{\circ}\text{C}$		3.9	1	V

Table 2. ELECTRICAL CHARACTERISTICS (T_J = 25° C unless otherwise stated) (continued)

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit		
DRAIN-SOURCE DIODE CHARACTERISTICS								
Reverse Recovery Time	t _{RR}	$V_{GS} = -5/20 \text{ V}, I_{SD} = 20 \text{ A},$		16.2		ns		
Reverse Recovery Charge	Q _{RR}	αι _S /αt = 1000 Α/μs		61.6		nC		
Reverse Recovery Energy	E _{REC}			4.1		μJ		
Peak Reverse Recovery Current	I _{RRM}			7.6		А		

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

TYPICAL CHARACTERISTICS



TYPICAL CHARACTERISTICS (continued)



TYPICAL CHARACTERISTICS (continued)



Figure 13. Junction-to-Case Transient Thermal Response Curve

MECHANICAL CASE OUTLINE PACKAGE DIMENSIONS

DURSEM







LAND PATTERN RECOMMENDATION



Г



٦

XXXXXXXXXX AYWWG
o

- XXXX = Specific Device Code А = Assembly Location Y = Year
- WW = Work Week
- G = Pb-Free Package

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "•", may or may not be present. Some products may not follow the Generic Marking.



DATE 16 AUG 2019

NOTES:

A. PACKAGE CONFORMS TO JEDEC TO-263 VARIATION CB EXCEPT WHERE NOTED. B. ALL DIMENSIONS ARE IN MILLIMETERS.

C OUT OF JEDEC STANDARD VALUE. D. DIMENSION AND TOLERANCE AS PER ASME Y14.5-2009. E. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH AND TIE BAR PROTRUSIONS.

	MILLIMETERS				
DIM	MIN	NOM	MAX		
Α	4.30	4.50	4.70		
A1	0.00	0.10	0.20		
b2	0.60	0.70	0.80		
b	0.51	0.60	0.70		
С	0.40	0.50	0.60		
c2	1.20	1.30	1.40		
D	9.00	9.20	9.40		
D1	6.15	6.80	7.15		
E	9.70	9.90	10.20		
E1	7.15	7.65	8.15		
е	1	1.27	~		
Н	15.10	15.40	15.70		
L	2.44	2.64	2.84		
L1	1.00	1.20	1.40		
L3	~	0.25	~		
aaa	~	~	0.25		



DOCUMENT NUMBER:	98AON84234G	Electronic versions are uncontrolled except when accessed directly from the Document Reposite Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	D ² PAK7 (TO-263-7L HV)		PAGE 1 OF 1	

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or indental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs,

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: <u>www.onsemi.com/support</u> For additional information, please contact your local Sales Representative at <u>www.onsemi.com/support/sales</u>