

Silicon Carbide (SiC) MOSFET – EliteSiC, 13 mohm, 1200 V, M3S, Die NTCR013N120M3S

Description

Silicon Carbide (SiC) MOSFET uses a completely new technology that provides superior switching performance and higher reliability compared to Silicon. In addition, the low ON resistance and compact chip size ensure low capacitance and gate charge. Consequently, system benefits include highest efficiency, faster operation frequency, increased power density, reduced EMI, and reduced system size.

Features


- Typ. $R_{DS(on)} = 13\text{ m}\Omega$ @ $V_{GS} = 18\text{ V}$
- Low Switching Losses (Typ. $E_{ON} 563\text{ J}$ at $75\text{ A}, 800\text{ V}$)

Applications


- Solar Inverters
- Electric Vehicle Charging Stations
- Uninterruptible Power Supplies (UPS)
- Energy Storage Systems
- Switch Mode Power Supplies (SMPS)

$V_{(BR)DSS}$	$R_{DS(on)}$ TYP	I_D MAX
1200 V	13 m Ω @ 18 V	151 A

N-CHANNEL MOSFET



DIE DIAGRAM




Die Information


- Wafer Diameter 6 inch
- Die Size 4,380 x 6,380 μm
- Metallization
 - Top Al/Si/Cu 5 μm
 - Back Ti/NiV/Ag 0.5 μm
- Die Thickness Typ. 100 μm
- Gate Pad Size 1300 x 1068 μm

NTCR013N120M3S

Die Layout



Die Cross Section



Passivation Information

- Passivation Material: Polyimide (PSP)
- Passivation Type: Local Passivation
- Passivation Thickness 15 μm
- : Passivation Area

Die Layout




Figure 1. Bare Die Dimensions

1. Based on TO-247 package of **onsemi**
2. Tested 100% on wafer
3. Sawn-on-film frame packing based on wafer tested

For Additional Product Information and Electrical Characteristics on Package Refer to the NTH4L013N120M3S product datasheet.

ORDERING INFORMATION AND PACKAGE MARKING

Part Number	Package	Packing Method
NTCR013N120M3S	Die	Wafer sawn-on-film

NTCR013N120M3S

THERMAL CHARACTERISTICS

Parameter	Symbol	Typ	Max	Unit
Junction-to-Case – Steady State (Note 4)	$R_{\theta JC}$	0.17	0.22	°C/W
Junction-to-Ambient – Steady State (Note 4)	$R_{\theta JA}$	–	40	

ELECTRICAL CHARACTERISTICS ($T_J = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
-----------	--------	----------------	-----	-----	-----	------

OFF-STATE CHARACTERISTICS

Drain-to-Source Breakdown Voltage	$V_{(BR)DSS}$	$V_{GS} = 0\text{ V}, I_D = 1\text{ mA}$	1200	–	–	V
Drain-to-Source Breakdown Voltage Temperature Coefficient	$V_{(BR)DSS}/T_J$	$I_D = 1\text{ mA}$, referenced to 25°C (Note 9)	–	0.3	–	V/°C
Zero Gate Voltage Drain Current	I_{DSS}	$V_{GS} = 0\text{ V}, V_{DS} = 1200\text{ V}, T_J = 25^\circ\text{C}$	–	–	100	μA
Gate-to-Source Leakage Current	I_{GSS}	$V_{GS} = +22/-10\text{ V}, V_{DS} = 0\text{ V}$	–	–	± 1	μA

ON-STATE CHARACTERISTICS (Note 5)

Gate Threshold Voltage	$V_{GS(TH)}$	$V_{GS} = V_{DS}, I_D = 37\text{ mA}$	2.04	2.8	4.4	V
Recommended Gate Voltage	V_{GOP}		–3	–	+18	V
Drain-to-Source On Resistance	$R_{DS(on)}$	$V_{GS} = 18\text{ V}, I_D = 75\text{ A}, T_J = 25^\circ\text{C}$	–	13	20	m Ω
		$V_{GS} = 18\text{ V}, I_D = 75\text{ A}, T_J = 175^\circ\text{C}$ (Note 9)	–	29	–	
Forward Transconductance	g_{FS}	$V_{DS} = 10\text{ V}, I_D = 75\text{ A}$ (Note 9)	–	57	–	S

CHARGES, CAPACITANCES & GATE RESISTANCE

Input Capacitance	C_{ISS}	$V_{GS} = 0\text{ V}, f = 1\text{ MHz}, V_{DS} = 800\text{ V}$ (Note 9)	–	5813	–	pF
Output Capacitance	C_{OSS}		–	262	–	
Reverse Transfer Capacitance	C_{RSS}		–	21	–	
Total Gate Charge	$Q_{G(TOT)}$	$V_{GS} = -3/18\text{ V}, V_{DS} = 800\text{ V}, I_D = 75\text{ A}$ (Note 9)	–	254	–	nC
Threshold Gate Charge	$Q_{G(TH)}$		–	37	–	
Gate-to-Source Charge	Q_{GS}		–	46	–	
Gate-to-Drain Charge	Q_{GD}		–	61	–	
Gate-Resistance	R_G		$f = 1\text{ MHz}$	–	1.4	

SWITCHING CHARACTERISTICS

Turn-On Delay Time	$t_{d(ON)}$	$V_{GS} = -3/18\text{ V}, V_{DS} = 800\text{ V}, I_D = 75\text{ A}, R_G = 4.7\text{ }\Omega$ Inductive load (Notes 8, 9)	–	22	–	ns
Rise Time	t_r		–	23	–	
Turn-Off Delay Time	$t_{d(OFF)}$		–	56	–	
Fall Time	t_f		–	10	–	
Turn-On Switching Loss	E_{ON}		–	563	–	μJ
Turn-Off Switching Loss	E_{OFF}		–	390	–	
Total Switching Loss	E_{tot}		–	953	–	

SOURCE-DRAIN DIODE CHARACTERISTICS

Continuous Source-Drain Diode Forward Current	I_{SD}	$V_{GS} = -3\text{ V}, T_C = 25^\circ\text{C}$ (Note 9)	–	–	151	A
Pulsed Source-Drain Diode Forward Current (Note 5)	I_{SDM}		–	–	505	
Forward Diode Voltage	V_{SD}	$V_{GS} = -3\text{ V}, I_{SD} = 75\text{ A}, T_J = 25^\circ\text{C}$	–	4.7	–	V

NTCR013N120M3S

ELECTRICAL CHARACTERISTICS ($T_J = 25^\circ\text{C}$ unless otherwise specified) (continued)

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
SOURCE-DRAIN DIODE CHARACTERISTICS						
Reverse Recovery Time	t_{RR}	$V_{GS} = -3/18\text{ V}$, $I_{SD} = 75\text{ A}$, $di_S/dt = 1000\text{ A}/\mu\text{s}$, $V_{DS} = 800\text{ V}$ (Note 9)	-	29	-	ns
Reverse Recovery Charge	Q_{RR}		-	252	-	nC
Reverse Recovery Energy	E_{REC}		-	26	-	μJ
Peak Reverse Recovery Current	I_{RRM}		-	18	-	A
Charge Time	T_A		-	17	-	ns
Discharge Time	T_B		-	12	-	ns

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
5. Repetitive rating, limited by max junction temperature.
6. The maximum current rating is based on typical $R_{DS(on)}$ performance.
7. E_{AS} of 800 mJ is based on starting $T_J = 25^\circ\text{C}$; $L = 1\text{ mH}$, $I_{AS} = 40\text{ A}$, $V_{DD} = 100\text{ V}$, $V_{GS} = 18\text{ V}$.
8. E_{ON}/E_{OFF} result is with body diode.
9. Defined by design, not subject to production test.

NTCR013N120M3S

TYPICAL CHARACTERISTICS




Figure 2. On-Region Characteristics




Figure 3. Normalized On-Resistance vs. Drain Current and Gate Voltage




Figure 4. On-Resistance Variation with Temperature




Figure 5. On-Resistance vs. Gate-to-Source Voltage




Figure 6. Transfer Characteristics




Figure 7. Switching Loss vs. Drain Current

NTCR013N120M3S

TYPICAL CHARACTERISTICS




Figure 8. Switching Loss vs. Drain-to-Source Voltage




Figure 9. Switching Loss vs. Gate Resistance




Figure 10. Switching Loss vs. Temperature




Figure 11. Reverse Drain Current vs. Body Diode Forward Voltage




Figure 12. Gate-to-Source Voltage vs. Total Charge




Figure 13. Capacitance vs. Drain-to-Source Voltage

NTCR013N120M3S

TYPICAL CHARACTERISTICS




Figure 14. Unclamped Inductive Switching Capability




Figure 15. Maximum Continuous Drain Current vs. Case Temperature




Figure 16. Safe Operating Area




Figure 17. Single Pulse Maximum Power Dissipation




Figure 18. Junction-to-Case Transient Thermal Response

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales