onsemi

<u>Silicon Carbide (SiC)</u> <u>MOSFET</u> – 80 mohm, 1200 V, M1, TO-247-3L

NVHL080N120SC1

Features

- Typ. $R_{DS(on)} = 80 \text{ m}\Omega$
- Ultra Low Gate Charge (typ. $Q_{G(tot)} = 56 \text{ nC}$)
- Low Effective Output Capacitance (typ. C_{oss} = 80 pF)
- 100% UIL Tested
- AEC–Q101 Qualified and PPAP Capable
- This Device is Halide Free and RoHS Compliant with exemption 7a, Pb–Free 2LI (on second level interconnection)

Typical Applications

- Automotive On Board Charger
- Automotive DC-DC converter for EV/HEV

MAXIMUM RATINGS (T_J = 25° C unless otherwise noted)

Parameter		Symbol	Value	Unit	
Drain-to-Source Voltage			V _{DSS}	1200	V
Gate-to-Source Voltage			V _{GS}	-15/+25	V
Recommended Opera- tion Values of Gate-to- Source Voltage	T _C < 175°C		V _{GSop}	-5/+20	V
Continuous Drain Current $R_{\theta JC}$	Steady State	$T_C = 25^{\circ}C$	Ι _D	31	A
Power Dissipation $R_{\theta JC}$			PD	178	W
Continuous Drain Current $R_{\theta JC}$	Steady T _C = 100°C State		Ι _D	22	A
Power Dissipation $R_{\theta JC}$			PD	89	W
Pulsed Drain Current (Note 2)	$T_A = 25^{\circ}C$		I _{DM}	132	A
Single Pulse Surge Drain Current Capability	$\begin{array}{l} T_{A}=25^{\circ}C,t_{p}=10\;\mu s,\\ R_{G}=4.7\;\Omega \end{array}$		I _{DSC}	132	A
Operating Junction and Storage Temperature Range		T _J , T _{stg}	–55 to +175	°C	
Source Current (Body Diode)			I _S	18	А
Single Pulse Drain–to–Source Avalanche Energy ($I_{L(pk)}$ = 18.5 A, L = 1 mH) (Note 3)			E _{AS}	171	mJ

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Case (Note 1)	$R_{\theta JC}$	0.84	°C/W
Junction-to-Ambient (Note 1)	$R_{\theta JA}$	40	°C/W


1. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.

2. Repetitive rating, limited by max junction temperature.

3. E_{AS} of 171 mJ is based on starting T_J = 25°C; L = 1 mH, I_{AS} = 18.5 A, V_{DD} = 120 V, V_{GS} = 18 V.


V _{(BR)DSS}	R _{DS(on)} MAX	I _D MAX
1200 V	110 mΩ @ 20 V	31 A

N-CHANNEL MOSFET





MARKING DIAGRAM



ORDERING INFORMATION

Device	Package	Shipping
NVHL080N120SC1	TO247-3L	30 Units / Tube

ELECTRICAL CHARACTERISTICS

Parameter	Symbol	Test Conditions	Min	Тур	Max	Unit
OFF CHARACTERISTICS	·			-		-
Drain-to-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} = 0 V, I _D = 1 mA	1200	-	-	V
Drain-to-Source Breakdown Voltage Temperature Coefficient	V _{(BR)DSS} /T _J	$I_D = 1 \text{ mA}$, referenced to 25°C	_	700	-	mV/°C
Zero Gate Voltage Drain Current	I _{DSS}	I_{DSS} $V_{GS} = 0 V, V_{DS} = 1200 V, T_{J} = 25^{\circ}C$	-	-	100	μA
		V_{GS} = 0 V, V_{DS} = 1200 V, T_{J} = 175°C	-	-	1	mA
Gate-to-Source Leakage Current	I _{GSS}	V_{GS} = +25/-15 V, V_{DS} = 0 V	-	-	±1	μA
ON CHARACTERISTICS						
Gate Threshold Voltage	V _{GS(th)}	$V_{GS} = V_{DS}, I_D = 5 \text{ mA}$	1.8	2.7	4.3	V
Recommended Gate Voltage	V _{GOP}		-5	-	+20	V
Drain-to-Source On Resistance	R _{DS(on)}	V_{GS} = 20 V, I _D = 20 A, T _J = 25°C	-	80	110	mΩ
		V_{GS} = 20 V, I _D = 20 A, T _J = 150°C	-	114	-	
Forward Transconductance	9 _{FS}	V _{DS} = 20 V, I _D = 20 A	-	13	-	S
CHARGES, CAPACITANCES & GATE	RESISTANCE					
Input Capacitance	C _{ISS}	V_{GS} = 0 V, f = 1 MHz, V_{DS} = 800 V	-	1112	-	pF
Output Capacitance	C _{OSS}		-	80	-	
Reverse Transfer Capacitance	C _{RSS}		-	6.5	-	
Total Gate Charge	Q _{G(tot)}	$V_{GS} = -5/20$ V, $V_{DS} = 600$ V, $I_D = 20$ A	-	56	-	nC
Gate-to-Source Charge	Q _{GS}		-	11	-	
Gate-to-Drain Charge	Q _{GD}		-	12	-	
Gate Resistance	R _G	f = 1 MHz	-	1.7	-	Ω
SWITCHING CHARACTERISTICS					•	
Turn-On Delay Time	t _{d(on)}	$V_{GS} = -5/20 \text{ V}, V_{DS} = 800 \text{ V},$	-	13	-	ns
Rise Time	t _r	$I_D = 20 \text{ A}, \text{ R}_G = 4.7 \Omega,$ Inductive Load	-	20	-	
Turn-Off Delay Time	t _{d(off)}		-	22	-	
Fall Time	t _f		-	10	-	
Turn-On Switching Loss	E _{ON}		-	258	-	μJ
Turn-Off Switching Loss	E _{OFF}		_	52	-	-
Total Switching Loss	E _{TOT}		-	311	-	
DRAIN-SOURCE DIODE CHARACTE	RISTICS					
Continuous Drain-to-Source Diode Forward Current	I _{SD}	V_{GS} = -5 V, T_{J} = 25 °C	-	_	18	A
Pulsed Drain-to-Source Diode Forward Current (Note 2)	I _{SDM}	V_{GS} = -5 V, T_{J} = 25 °C	-	-	132	A
Forward Diode Voltage	V _{SD}	V_{GS} = –5 V, I_{SD} = 10 A, T_J = 25 $^\circ C$	-	4	-	V
Reverse Recovery Time	t _{RR}	V _{GS} = -5/20 V, I _{SD} = 20 A, dI _S /dt = 1000 A/μs	-	16	-	ns
Reverse Recovery Charge	Q _{RR}		-	62	-	nC
Reverse Recovery Energy	E _{REC}		-	5	-	μJ
Peak Reverse Recovery Current	I _{RRM}		_	8	_	А

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.




Figure 1. On Region Characteristics






Figure 2. Normalized On-Resistance vs. Drain **Current and Gate Voltage**












Figure 4. On-Resistance vs. Gate-to-Source Voltage




Figure 6. Source-to-Drain Diode Forward Voltage vs. Source Current




Figure 7. Gate Charge Characteristics








Figure 8. Capacitance vs. Drain-to-Source Voltage












Figure 10. Maximum Continuous Drain **Current vs. Case Temperature**




Figure 12. Single Pulse Maximum Power Dissipation

TYPICAL CHARACTERISTICS ($T_J = 25^{\circ}C$ unless otherwise noted) (continued)




Figure 13. Junction-to-Case Transient Thermal Response Curve



6.60 6.80 7.00 Electronic versions are uncontrolled except when accessed directly from the Document Repository. **DOCUMENT NUMBER:** 98AON93302G Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. **DESCRIPTION:** TO-247-3LD PAGE 1 OF 1

not follow the Generic Marking.

ON Semiconductor and 💷 are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

~

12.81

~

E1

ØP1



D2

ON Semiconductor

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent_Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or indental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs,

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: <u>www.onsemi.com/support</u> For additional information, please contact your local Sales Representative at <u>www.onsemi.com/support/sales</u>