

# Monolithic Microwave Integrated Circuits (MMIC)

Amplifier, 3 V, 6 mA, 0.1 to 2.8 GHz, MCPH6

## **SMA3107**

#### **Features**

High Gain: G<sub>p</sub> = 23.5 dB typ. @1 GHz
 Wideband Response: f<sub>u</sub> = 2.8 GHz
 Low Current: I<sub>CC</sub> = 6 mA typ
 Port Impedance: Input/Output 50 Ω

• This is a Pb-Free Device

## ABSOLUTE MAXIMUM RATINGS (T<sub>A</sub> = 25°C unless otherwise noted)

| Symbol           | Parameter                   | Ratings     | Unit |
|------------------|-----------------------------|-------------|------|
| V <sub>CC</sub>  | Supply Voltage              | 5           | V    |
| I <sub>CC</sub>  | Circuit Current             | 15          | mA   |
| $P_{D}$          | Allowable Power Dissipation | 280         | mW   |
| T <sub>opr</sub> | Operating Temperature       | -40 to +85  | °C   |
| T <sub>STG</sub> | Storage Temperature         | -55 to +150 | °C   |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

#### RECOMMENDED OPERATING CONDITION

(T<sub>A</sub> = 25°C unless otherwise noted)

|                  |                               | Ratings |     |     |      |
|------------------|-------------------------------|---------|-----|-----|------|
| Symbol           | Parameter                     | Min     | Тур | Max | Unit |
| V <sub>CC</sub>  | Supply Voltage                | 2.7     | 3   | 3.3 | V    |
| T <sub>opr</sub> | Operating Ambient Temperature | -40     | +25 | +85 | °C   |



SC-88FL / MCPH6 CASE 419AS

## **MARKING DIAGRAM**



LE = Specific Device Code

#### **ORDERING INFORMATION**

| Device       | Package            | Shipping <sup>†</sup> |
|--------------|--------------------|-----------------------|
| SMA3107-TL-E | MCPH6<br>(Pb-Free) | 3000 /<br>Tape & Reel |

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, <a href="https://example.com/BRD8011/D">BRD8011/D</a>.

## **SMA3107**

## **ELECTRICAL CHARACTERISTICS** (T<sub>A</sub> = 25°C, V<sub>CC</sub> = 3 V, Z<sub>s</sub> = Z<sub>L</sub> = 50 $\Omega$ )

|                     |                                       | Conditions                              | Ratings |      |      |      |
|---------------------|---------------------------------------|---|---------|------|------|------|
| Symbol              | Parameter                             |   | Min     | Тур  | Max  | Unit |
| I <sub>CC</sub>     | Circuit Current                       |   | 4.3     | 6.0  | 7.7  | mA   |
| G <sub>p</sub>      | Power Gain                            | f = 1 GHz                               | 21.0    | 23.5 | 26.0 | dB   |
|                     |                                       | f = 2.2 GHz                             | 22.0    | 24.5 | 27.0 |      |
| I <sub>SL</sub>     | Isolation                             | f = 1 GHz                               | 33.0    | 38.0 | -    | dB   |
|                     |                                       | f = 2.2 GHz                             | 40.0    | 45.0 | -    | dB   |
| $R_{Lin}$           | Input Return Loss                     | f = 1 GHz                               | 18.0    | 23.0 | -    | dB   |
|                     |                                       | f = 2.2 GHz                             | 10.0    | 13.0 | -    |      |
| R <sub>Lout</sub>   | Output Return Loss                    | f = 1 GHz                               | 27.0    | 32.0 | -    | dB   |
|                     |                                       | f = 2.2 GHz                             | 10.0    | 13.0 | -    | dB   |
| NF                  | Noise Figure                          | f = 1 GHz                               | _       | 3.1  | 4.3  | dB   |
|                     |                                       | f = 2.2 GHz                             | -       | 3.6  | 4.3  |      |
| P <sub>o(1dB)</sub> | Gain 1 dB Compression<br>Output Power | f = 1 GHz                               | -10     | -8   | -    | dBm  |
|                     |                                       | f = 2.2 GHz                             | -11.5   | -9.5 | -    |      |
| f <sub>u</sub>      | Upper Limit Operating<br>Frequency    | 3 dB down below fl at gain at f = 1 GHz | -       | 2.8  | -    | GHz  |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

NOTES: Pay attention to handling since it is liable to be affected by static electricity due to the high frequency process adopted.





Figure 1. Test Circuit

## SMA3107




| Symbol | Value   |
|--------|---------|
| C1, C2 | 100 pF  |
| СЗ     | 1000 pF |

Figure 2. Evaluation Board

## **SMA3107**

## TYPICAL PERFORMANCE CHARACTERISTICS



## TYPICAL PERFORMANCE CHARACTERISTICS (continued)




Figure 9. Pout - Pin




Figure 10. S Parameter, S11





Figure 11. S Parameter, S22






## SC-88FL / MCPH6 CASE 419AS ISSUE A

**DATE 28 SEP 2022** 







He

SIDE VIEW

BOTTOM VIEW







- NO INDUSTRY STANDARD APPLIES TO THIS PACKAGE.
- 2. ALL DIMENSIONS ARE IN MILLIMETERS.
- DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH AND THE BAR PROTRUSIONS.

| MIG   | MILLIMETERS |      |      |  |
|-------|-------------|------|------|--|
| ابالط | MIN.        | N□M. | MAX. |  |
| Α     | 0.80        | 0.85 | 0.90 |  |
| A1    | 0.00        |      | 0.02 |  |
| b     | 0.25        | 0.30 | 0.40 |  |
| C     | 0.12        | 0.15 | 0.25 |  |
| D     | 1.94        | 2.00 | 2.06 |  |
| E     | 1.54        | 1.60 | 1.66 |  |
| He    | 2.05        | 2.10 | 2.15 |  |
| L     | 0.19        | 0.25 | 0.31 |  |
| L1    | 0.00        | 0.07 | 0.12 |  |
| 6     | 0.65 BSC    |      |      |  |

## GENERIC MARKING DIAGRAM\*



XXX = Specific Device Code

M = Date Code ■ = Pb-Free Package

(Note: Microdot may be in either location)

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "•", may or may not be present. Some products may not follow the Generic Marking.

| DOCUMENT NUMBER: | 98AON65646E     | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |             |  |
|------------------|-----------------|---|-------------|--|
| DESCRIPTION:     | SC-88FL / MCPH6 |   | PAGE 1 OF 1 |  |

onsemi and ONSEMI are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, Onsemi, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA class 3 medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase

#### ADDITIONAL INFORMATION

**TECHNICAL PUBLICATIONS:** 

 $\textbf{Technical Library:} \ \underline{www.onsemi.com/design/resources/technical-documentation}$ 

onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at

www.onsemi.com/support/sales