Plastic Silicon OPTOLOGIC Photosensor

QSE257, QSE259

SIDELOOKER OPTOLOGIC
CASE 100CL

Description

The QSE25x family are OPTOLOGIC ICs which feature a Schmitt trigger at output which provides hysteresis for noise immunity and pulse shaping. The basic building block of this IC consists of a photodiode, a linear amplifier, voltage regulator, Schmitt trigger and four output options. The TTL/LSTTL compatible output can drive up to ten TTL loads over supply currents from 4.5 to 16.0 Volts. The devices are marked with a color stripe for easy identification.

Features

- Bipolar Silicon IC
- Package Type: Sidelooker
- Medium Wide Reception Angle, 50°
- Package Material and Color: Black Epoxy
- Daylight Filter
- High Sensitivity
- Direct TTL/LSTTL Interface
- These are Pb−Free Devices

Block Diagrams



Figure 1. QSE257 Totem−Pole Output Inverter



Figure 2. QSE259 Open−Collector Output Inverter

INPUT/OUTPUT TABLE

Part Number	Light	Output
QSE257	On	LOW
	Off	HIGH
QSE259	On	LOW
	Off	HIGH

ORDERING INFORMATION

See detailed ordering and shipping information on page 5 of this data sheet.

MAXIMUM RATINGS (T_A = 25°C unless otherwise specified)

Symbol	Parameter	Rating	Unit
T_{OPR}	Operating Temperature	−40 to +85	°C
T_{STG}	Storage Temperature	−40 to +100	°C
T_{SOL-I}	Soldering Temperature (Iron) (Notes 2, 3, 4)	240 for 5 s	°C
T_{SOL-F}	Soldering Temperature (Flow) (Notes 2, 3)	260 for 10 s	°C
I_O	Output Current	50	mA
V_{CC}	Supply Voltage	4.0 to 16	V
V_O	Output Voltage	35	V
P_D	Power Dissipation (Note 1)	100	mW

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Derate power dissipation linearly 2.50 mW/°C above 25°C.
2. RMA flux is recommended.
3. Methanol or isopropyl alcohols are recommended as cleaning agents.
4. Soldering iron 1/16” (1.6 mm) minimum from housing.

ELECTRICAL CHARACTERISTICS (T_A = −40°C to +85°C, V_{CC} = 4.5 V to 5.5 V)

Symbol	Parameter	Test Condition	Min	Typ	Max	Unit
Ee(+)	Positive Going Threshold Irradiance (Note 5)	T_A = 25°C	0.025	–	0.250	mW/cm^2
Ee(+) / Ee(−)	Hysteresis Ratio		1.10	–	2.00	
I_{CC}	Supply Current (Note 5)	Ee = 0 or 0.3 mW/cm^2	–	–	5.0	mA
	Peak to Peak Ripple which will Cause False Triggering	f = DC to 50 MHz	–	–	2.00	V
QSE257 (INVERTER TOTEM POLE)						
V_{OH}	High Level Output Voltage	Ee = 0, I_{OH} = −10 mA	2.4	–	–	V
V_{OL}	Low Level Output Voltage (Note 5)	Ee = 0.3 mW/cm^2, I_{OL} = 16 mA	–	–	0.40	V
QSE259 (INVERTER OPEN COLLECTOR)						
I_{OH}	High Level Output Voltage	Ee = 0, V_{OH} = 30 V	–	–	100	μA
V_{OL}	Low Level Output Voltage (Note 5)	Ee = 0.3 mW/cm^2, I_{OL} = 16 mA	–	–	0.40	V
QSE257						
t_R, t_F	Output Rise, Fall Times	Ee = 0 or 0.3 mW/cm^2, f = 10 kHz, DC = 50%, R_L = 360 Ω (Note 5)	–	–	70	ns
t_{PHL}, t_{PLH}	Propagation Delay		–	6.0	–	μs
QSE259						
t_R, t_F	Output Rise, Fall Times	Ee = 0 or 0.3 mW/cm^2, f = 10 kHz, DC = 50%, R_L = 360 Ω (Note 5)	–	–	100	ns
t_{PHL}, t_{PLH}	Propagation Delay		–	6.0	–	μs

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

5. λ = 880 nm (AlGaAs).

TYPICAL PERFORMANCE CURVES

(Sensor Coupled to QEE113 Emitter)



Figure 3. Output Voltage vs. Input Current



Figure 4. Threshold Current vs. Distance



Figure 5. Normalized Threshold Current vs. Supply Voltage

TYPICAL PERFORMANCE CURVES (continued)

(Sensor Coupled to QEE113 Emitter)



Figure 6. Normalized Threshold Current vs. Ambient Temperature



Figure 7. Low Output Voltage vs. Output Current



Figure 8. Response Time vs. Forward Current



R_1 = 360 Ω
R_2 = 180 Ω

C_1 = 15 pF
C_2 = 20 pF

C_1 and C_2 include probe and stray wire capacitance

Figure 9. Switching Speed Test Circuit



Figure 10. Switching Times Definitions

ORDERING INFORMATION

Part Number	Package	Part Number Definitions	Color Code	Shipping
QSE257	SIDELOOKER OPTOLOGIC (Pb−Free)	Totem−Pole, inverter output	Yellow	500 Units / Bulk
QSE259		Open−collector, inverter output	Blue	

SIDELOOKER OPTOLOGIC
CASE 100CL
ISSUE O

DATE 30 NOV 2016



Note:

1. Dimensions for all drawings are in millimeters.

DOCUMENT NUMBER:	**98AON13426G**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	**SIDELOOKER OPTOLOGIC**	**PAGE 1 OF 1**

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales