NOTE 4 D

NOTE 6

Α

В

**TOP VIEW** 

SIDE VIEW

H H H H H H H H H H

**BOTTOM VIEW** 

RECOMMENDED

SOLDERING FOOTPRINT\*

**←**3.00→

NOTE 8 D2 3

NOTE 6

E1

PIN 1— REFERENCE

е

 $\oplus$  0.15  $\oplus$  C A-B D



0.20

NOTE 5

0.10 C

0.10 C

## SSOP-24 NB EP CASE 940AQ **ISSUE 0**

0.20 C A-B

Н

△ 0.20 C

2X 12 TIPS

C SEATING PLANE

⊕ 0.15 M C A-B

⊕ 0.12 M C A-B D

D

Ε

24X **b** 

**DATE 18 AUG 2017** 

L2

GAUGE

PLANE

C SEATING PLANE

**DETAIL A** 


**DETAIL A** 

**END VIEW** 

NOTF 7

- 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994. 2. CONTROLLING DIMENSION: MILLIMETERS.
- 3. DIMENSION b DOES NOT INCLUDE DAMBAR PROTRUSION. DAMBAR PROTRUSION SHALL BE 0.10 MAX. AT MMC. DAMBAR CANNOT BE LOCATED ON THE LOWER RADIUS OF THE FOOT. DIMENSION & APPLIES TO THE FLAT SECTION OF THE LEAD BETWEEN 0.10 TO 0.25 FROM THE LEAD TIP.
- DIMENSION D DOES NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS. MOLD FLASH, PROTRUSIONS OR GATE BURRS SHALL NOT EXCEED 0.15 PER SIDE. DIMENSION D IS DETERMINED AT DATUM PLANE H.
  5. DIMENSION E1 DOES NOT INCLUDE INTERLEAD
- FLASH OR PROTRUSION. INTERLEAD FLASH OR PROTRUSION SHALL NOT EXCEED 0.25 PER SIDE. DIMENSION E1 IS DETERMINED AT DA-TUM PLANE H.
- 6. DATUMS A AND B ARE DETERMINED AT DATUM PLANE H.
  A1 IS DEFINED AS THE VERTICAL DISTANCE
- FROM THE SEATING PLANE TO THE LOWEST POINT ON THE PACKAGE BODY.
- CONTOURS OF THE THERMAL PAD ARE UN-CONTROLLED WITHIN THE REGION DEFINED BY DIMENSIONS D2 AND E2.

MILLIMETERS	
MIN	MAX
-	1.75
0.00	0.10
1.10	1.65
0.19	0.30
0.09	0.20
8.64	BSC
2.50	2.70
6.00	BSC
3.90	BSC
1.80	2.00
0.65	BSC
0.25	0.50
0.40	0.85
1.00	REF
0.25 BSC	
0°	8°
	MIN 0.00 1.10 0.19 0.09 8.64 2.50 6.00 3.90 1.80 0.65 0.25 0.40 1.00 0.25



## **GENERIC MARKING DIAGRAM\***



XXXX = Specific Device Code

= Assembly Location

WL = Wafer Lot YY = Year WW = Work Week

= Pb-Free Package

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot " ■", may or may not be present. Some products may not follow the Generic Marking.

## SCALE 1:1

*For additional information on our Pb-Free strategy and soldering
details, please download the ON Semiconductor Soldering and
Mounting Techniques Reference Manual, SOLDERRM/D.

0.65

**PITCH** 

Electronic versions are uncontrolled except when accessed directly from the Document Repository. **DOCUMENT NUMBER:** 98AON73645G Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.

**DESCRIPTION:** SSOP-24 NB EP

2.20 6.40

**DIMENSIONS: MILLIMETERS** 

**PAGE 1 OF 1** 

ON Semiconductor and un are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the